

## Appendix I: Packing for Shipment

If you ship the CTS850, pack it in the original shipping carton and packing material. If the original packing material is not available, package the instrument as follows:

1. Obtain a corrugated cardboard shipping carton with inside dimensions at least 15 cm (6 in) taller, wider, and deeper than the CTS850. The shipping carton must be constructed of cardboard with 170 kg (375 lb) test strength.
2. If you are shipping the CTS850 to a Tektronix field office for repair, attach a tag to the CTS850 showing the instrument owner and address, the name of the person to contact about the instrument, the instrument type, and the serial number.
3. Wrap the CTS850 with polyethylene sheeting or equivalent material to protect the finish.
4. Cushion the CTS850 in the shipping carton by tightly packing dunnage or urethane foam on all sides between the carton and the CTS850. Allow 7.5 cm (3 in) on all sides, top, and bottom.
5. Seal the shipping carton with shipping tape or an industrial stapler.

