

Strain Gage Adhesive for Stress Analysis and Transducer Applications

OTHER ACCESSORIES USED IN AN M-BOND 43-B INSTALLATION:

- CSM Degreaser or GC-6 Isopropyl Alcohol
- Silicon-Carbide Paper
- M-Prep Conditioner A
- M-Prep Neutralizer 5A
- GSP-1 Gauze Sponges
- CSP-1 Cotton Tip Applicators
- MJG-2 Mylar® Tape
- TFE-1 Teflon® Film
- HSC Spring Clamp
- GT-14 Pressure Pads and Backup Plates



RoHS
COMPLIANT

DESCRIPTION

Single-component, solvent-thinned, epoxy adhesive normally used in transducer applications; solids content 25%. May be used both as an adhesive and as a

protective coating. Capable of forming very thin, hard, void-free gluelines similar to M-Bond 610. Highly resistant to moisture and chemical attack.

| CHARACTERISTICS | |
|-----------------------------|---|
| PARAMETER | DETAILS |
| OPERATING TEMPERATURE RANGE | Short Term: -452° to +350°F (-269° to +175°C) Long Term: -452° to +300°F (-269° to +150°C) Transducers: to +250°F (+120°C). |
| ELONGATION CAPABILITIES | 1% at -452°F (-269°C), 4% at +75°F (+24°C), 2% at +300°F (+150°C). |
| SHELF LIFE | 13 months from the date of manufacture on the label (minimum published 9 months) when stored unmixed at +75°F (+24°C); or 22 months from the date of manufacture on the label (minimum published 18 months) when stored unmixed refrigerated upon receipt at +40°F (+5°C). Refer to product label. |
| POT LIFE | Minimum 9 months at +75°F (+24°C); or 18 months at +40°F (+5°C). |
| CLAMPING PRESSURE | For Stress Analysis: 15 to 100 psi (100 to 700 kN/m ²). Optimum: 40 to 50 psi (275 to 350 kN/m ²). For Transducers: 45 to 60 psi (315 to 415 kN/m ²). Optimum: 50 psi (350 kN/m ²). |
| CURE REQUIREMENTS* | 2 hours at +375°F (+190°C), or as an alternate cure for aluminum alloy transducers, 2-1/2 hours at +300°F (+150°C). Recommended Postcure: 2 hours at +400°F (+205°C), or as an alternate postcure for aluminum alloy transducer applications, 2-1/2 hours at +350°F (+175°C). |

| PACKAGING | |
|--|---|
| KIT | SINGLE BOTTLE |
| 4 brush-cap bottles (30 ml ea) premixed adhesive | 1 brush-cap bottle (30 ml ea) premixed adhesive |

* **Reference:** Instruction Bulletin B-130, "Strain Gage Installations with M-Bond 43-B, 600 and 610 Adhesive Systems", included in each kit.

Mylar and Teflon are Registered Trademarks of DuPont

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.