

## **Quarterly Reliability Monitoring Results**

## Quarters: Q1/2021 to Q4/2021

Based on structural similarity

| Supplier                          |   | User Part Number  |                                   |           |            |           |  |  |
|-----------------------------------|---|---|-----------------------------------|-----------|------------|-----------|--|--|
| Nexperia B.V.  Name of Laboratory |   | BZX884-B20 Part Description   |                                   |           |            |           |  |  |
|                                   |   |   |                                   |           |            |           |  |  |
| Assembly reliability labs         |   | MCD package   |                                   |           |            |           |  |  |
| Based on AEC-Q101 Test            |   | Test Conditions   | Duration                          | # Lots    | # Quantity | # Rejects |  |  |
|                                   | TEST  |   |                                   |           |            |           |  |  |
|                                   | Pre- and Post-Stress                                    |   |                                   |           |            |           |  |  |
| # E1                              | Electrical Test   | Tamb = 25 °C  | N/A                               | see below | all parts  | see below |  |  |
| # A1                              | <b>PC</b> Preconditioning                               | JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering                         | 24 hours<br>168 hours<br>3 cycles | 113       | 9040       | 0         |  |  |
| # B1                              | HTRB<br>High Temperature Reverse<br>Bias                | MIL-STD-750-1<br>M1038 Method A<br>Tj = Tjmax, Vr = 100% of max. datasheet<br>reverse voltage       | 1000 hours                        | 138       | 11040      | 0         |  |  |
| # B1b                             | SSOP Steady State Operational                           | MIL-STD-750-1<br>M1038 Method B<br>Tj = Tjmax, Iz = 100% of max. datasheet<br>reverse current       | 1000 hours                        | 20        | 1600       | 0         |  |  |
| # A4                              | TC<br>Temperature Cycling                               | JESD22-A104<br>-65 °C to Tjmax, not to exceed 150°C   | 1000 cycles                       | 28        | 2240       | 0         |  |  |
| # A3 alt                          | <b>AC</b><br>Autoclave                                  | JESD22-A102<br>Tamb = 121 °C, RH = 100 %<br>Pressure = 205 kPa (29.7 psia)                          | 96 hours                          | 28        | 2240       | 0         |  |  |
| # A2 alt                          | H3TRB<br>High Humidity High<br>Temperature Reverse Bias | JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage $^{[1]}$                     | 1000 hours                        | 28        | 2240       | 0         |  |  |
| # A5                              | IOL Intermittent Operating Life                         | MIL-STD-750 Method 1037 ton = toff, devices powered to insure $\Delta Tj$ = 100 °C for 15000 cycles | 1000 hours                        | 29        | 2320       | 0         |  |  |
| # C8                              | RSH<br>Resistance to Solder Heat                        | JESD22-A111<br>260 °C ± 5 °C  | 10 s                              | n.a.      | n.a.       | n.a.      |  |  |
| # C10                             | <b>SD</b><br>Solderability                              | J-STD-002   |                                   | 63        | 630        | 0         |  |  |

<sup>[1]</sup> The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

## **Calculation of FIT and MTTF**

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

| Wafer Fab | Technology | Quantity | Rejects | Failure Rate (FIT) | MTTF (hrs) |
|-----------|------------|----------|---------|--------------------|------------|
| Nexperia  |            |          |         |                    |            |
| DHAM      | Zener      | 11040    | 0       | 0.38               | 2.60E+09   |

<sup>© 2022</sup> Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com