nexperia

Quarterly Reliability Monitoring Results

Quarters: Q1/2021 to Q4/2021

Based on structural similarity

Supplier		User Part Number						
Nexperia B.V. Name of Laboratory Assembly reliability labs Based on AEC-Q101 Test		PDTA115EMB Part Description						
								Nexperia DHAM Small Signal Bipolar Transistor
		MCD package						
		Test Conditions	Duration	# Lots	# Quantity	# Rejects		
			TEST					
	Pre- and Post-Stress							
# E1	Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below		
# A1	PC Preconditioning	JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85% Reflow soldering	24 hours 168 hours 3 cycles	208	16640	0		
# B1	HTRB High Temperature Reverse Bias	MIL-STD-750-1 M1039 Method A Tj = Tjmax, Vr = 100% of max. datasheet reverse voltage	1000 hours	202	16160	0		
# A4	TC Temperature Cycling	JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	1000 cycles	52	4160	0		
# A3 alt	AC Autoclave	JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)	96 hours	52	4160	0		
<i>"</i> • • • •	H3TRB High Humidity High Temperature Reverse Bias	JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of		50		<u>^</u>		
# A2 alt	IOL	MIL-STD-750 Method 1037 ton = toff, devices powered to insure ΔT_i =	1000 hours	52	4160	0		
# A5	Intermittent Operating Life		1000 hours	52	4160	0		
	RSH	JESD22-A111						
# C8	Resistance to Solder Heat	260 °C ± 5 °C	10 s	n.a.	n.a.	n.a.		
# C10	SD Solderability	J-STD-002		111	1110	0		

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia DHAM	Small Signal Bipolar Transistor	16160	0	0.26	3.81E+09

© 2022 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any nexperia.com representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.