

Quarterly Reliability Monitoring Results

Quarters: Q1/2021 to Q4/2021

Based on structural similarity

Supplier Nexperia B.V. Name of Laboratory		User Part Number PDZ3.3B Part Description												
										Nexperia DHAM	Zener			
								Assembly reliability labs		SMD package				
Based on AEC-Q101 Test		Test Conditions	Duration	# Lots	# Quantity	# Rejects								
	TEST													
	Pre- and Post-Stress													
# E1	Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below								
	PC	JESD22-A113 Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85%	24 hours 168 hours											
# A1	Preconditioning	Reflow soldering	3 cycles	810	58300	0								
# B1	HTRB High Temperature Reverse Bias	MIL-STD-750-1 M1038 Method A Tj = Tjmax, Vr = 100% of max. datasheet reverse voltage	1000 hours	138	11040	0								
# B1b	SSOP Steady State Operational	MIL-STD-750-1 M1038 Method B Tj = Tjmax, Iz = 100% of max. datasheet reverse current	1000 hours	20	1600	0								
# A4	TC Temperature Cycling	JESD22-A104 -65 °C to Tjmax, not to exceed 150°C	1000 cycles	170	13600	0								
# A3 alt	AC Autoclave	JESD22-A102 Tamb = 121 °C, RH = 100 % Pressure = 205 kPa (29.7 psia)	96 hours	170	13600	0								
# A2 alt	H3TRB High Humidity High Temperature Reverse Bias	JESD22-A101 Tamb = 85 °C, RH = 85%, VR = 80 % of rated reverse voltage $^{[1]}$	1000 hours	170	13600	0								
# A5	IOL Intermittent Operating Life	MIL-STD-750 Method 1037 ton = toff, devices powered to insure $\Delta Tj = 100$ °C for 15000 cycles	1000 hours	170	13600	0								
# C8	RSH Resistance to Solder Heat	JESD22-A111 260 °C ± 5 °C	10 s	130	3900	0								
# C10	SD Solderability	J-STD-002		363	3630	0								

^[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

Wafer Fab	Technology	Quantity	Rejects	Failure Rate (FIT)	MTTF (hrs)
Nexperia					
DHAM	Zener	11040	0	0.38	2.60E+09

^{© 2022} Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.

nexperia.com