nexperia

Quarterly Reliability Monitoring Results

Quarters: Q1/2021 to Q4/2021

Based on structural similarity

Supplier		User Part Number					
Nexperia B.V	<i>r</i> .	PESD27VV2BT					
Name of L	aboratory	Part Description					
		Nexperia DHAM	Protection Bipolar				
Assembly re	eliability labs	SMD package					
Based on /	AEC-Q101 Test	Test Conditions	Duration	# Lots	# Quantity	# Quantity # Rejects	
	TEST						
	Pre- and Post-Stress						
# E1	Electrical Test	Tamb = 25 °C	N/A	see below	all parts	see below	
		JESD22-A113	241				
	PC	Bake Tamb = 125 °C Soak Tamb = 85 °C, RH = 85%	24 hours 168 hours				
# A1	Preconditioning	Reflow soldering	3 cycles	286	21480	0	
# AI		MIL-STD-750-1	5 676165	200	21400	0	
	HTRB	MIL-STD-750-1 M1038 Method A					
		$T_j = T_j max$, $Vr = 100\%$ of max. datasheet					
# B1	Bias	reverse voltage	1000 hours	23	1840	0	
						-	
	тс	JESD22-A104					
# A4	Temperature Cycling	-65 °C to Tjmax, not to exceed 150°C	1000 cycles	86	6880	0	
		JESD22-A102					
	AC	Tamb = 121 °C, RH = 100 %					
# A3 alt	Autoclave	Pressure = 205 kPa (29.7 psia)	96 hours	86	6880	0	
	H3TRB	JESD22-A101					
	High Humidity High	Tamb = 85 °C, RH = 85%, VR = 80 % of					
# A2 alt	Temperature Reverse Bias	rated reverse voltage ¹¹	1000 hours	86	6880	0	
		MIL-STD-750 Method 1037					
	IOL	ton = toff, devices powered to insure $\Delta T j$ =					
# A5	Intermittent Operating Life	100 °C for 15000 cycles	1000 hours	n.a.	n.a.	n.a.	
	BGU						
# 69	RSH Resistance to Solder Heat	JESD22-A111	10 -	20	0.40	0	
# C8		200 (± 3 °C	10 s	28	840	0	
# C10	SD Solderability	J-STD-002		26	260	0	
# C10	Soluerability	J-31D-002		36	360	0	

[1] The maximum applied voltage is limited by test chamber set up and does not exceed 115V.

Calculation of FIT and MTTF

Test considered for FIT calculation: High Temperature Reverse Bias (HTRB, Test #B1) Confidence level 60%, derated to 55 °C, activation energy 0.7 eV, test time 168 to 1000 hours

MTTF (hrs)	Failure Rate (FIT)	Rejects	Quantity	Technology	Wafer Fab
4.33E+08	2.31	0	1840	Protection Bipolar	Nexperia DHAM
	2.31	0	1840	Protection Bipolar	DHAM

© 2022 Nexperia B.V.

All information hereunder is per Nexperia's best knowledge. This document does not provide for any nexperia.com representation or warranty express or implied by Nexperia. In case Nexperia has tested the product, this documentation reflects the outcome of the analysis of the actually tested parts only.